Home Care Technical Specification

1 ¼" Grab Bars – Concealed Screw

8700

Stock Numbers:

- q **DN8712 12" Grab Bar** Satin Finish, 1 ¼" Bar, Concealed Screw Mounting
- q 8716CB, R8716PB 16" Grab Bar
 Chrome & Brass or Polished Brass Finish,
 1 ¼" Bar, Concealed Screw Mounting
- q 8718, R8718PS, R8718PB, R8718W –
 18" Grab Bar
 Satin, Polished Stainless, Polished Brass, or White Finish, 1 ¼" Bar,
 Concealed Screw Mounting
- a 8724, R8724PS, 8724CB, R8724PB, R8724W – 24" Grab Bar
 Satin, Polished Stainless, Chrome & Brass, Polished Brass, or White Finish, 1 ¼" Bar, Concealed Screw Mounting
- q 8730 30" Grab Bar
 Satin Finish, 1 ¼" Bar,
 Concealed Screw Mounting
- q 8732 32" Grab Bar
 Satin Finish, 1 ¼" Bar,
 Concealed Screw Mounting
- R8736PS, R8736PB, R8736W –
 36" Grab Bar
 Polished Stainless, Polished Brass or
 White Finish, 1 ¼" Bar,
 Concealed Screw Mounting
- q 8742, R8742PS 42" Grab Bar
 Satin or Polished Stainless Finish,
 1 ¼" Bar, Concealed Screw Mounting
- q 8748 48" Grab Bar
 Satin Finish, 1 ¼" Bar,
 Concealed Screw Mounting

Materials:

1 ¼" **Grab Bar** rods are formed from 18-gauge (.049) type 304 stainless steel tubing.

Dimensions:



Installation Instructions:

- 1. Position unit on wall in desired location.
- 2. Mark mounting holes.
- 3. Drill starter holes.
- 4. Mount unit on wall using 2 ¼" screws (provided).
- 5. Snap flange covers into place.

Note: Wood blocking is preferable behind all wall surfaces. If wood blocking is not available, the following optional fasteners are suggested: Tile/Masonry – Plastic or Lead Anchors; Plaster/Drywall – Toggle Bolts.

Stock Number:_____ By CSI Bath Furnishings 1 ¼" Grab Bars



25300 AL MOEN DRIVE • NORTH OLMSTED, OH 44070 (800) 321-8809 • FAX: (800) 848-6636 • INTERNATIONAL: (440) 962-2000 • FAX: (440) 962-2726 CUSTOMER SERVICE (USA): 800-882-0116 ©Copyright CSI Bath Furnishing Division of Moen 02/22/01