# **KOHLER**<sub>®</sub>

# Features

- End drain.
- Integral lumbar support and armrests for comfort.
- 60" (1524 mm) x 42" (1067 mm) x 21" (533 mm)

#### Material

Acrylic

#### Hydrotherapy

- Single-speed whirlpool offers six fully adjustable hydro-massage jets for water flow and direction.
- Pump with air switch for whirlpool.

# Installation

Drop-in

# **Recommended Accessories**

K-11677 Bath Drain K-1491 Bath/Whirlpool Pillow K-1601 Bath/Whirlpool Footstop K-576 Under-mount Install Kit K-24916 Wireless Music Kit K-7213 27" Cable Bath Drain K-7214 27" Cable Bath Drain K-37382 45" Rough-in Cable Bath Drain



# **Codes/Standards**

ASME A112.19.7/CSA B45.10 CSA B45.5/IAPMO Z124 ASTM E162 ASTM E662 UL 1795 Greenguard UL 2818 - Gold CARB P2

#### **KOHLER® One-Year Limited Warranty**

See website for detailed warranty information.

# Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White


-	
96	Biscuit

- 47 Almond
- G9 Sandbar



# Sunward® 5' Whirlpool Bath K-1162





#### **Required Electrical Service**

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

#### **Technical Information**

All product dimensions are nominal.

Installation:	Drop-in
Drain location:	End
Basin area, bottom:	43" x 21-9/16" (1092 mm x 548 mm)
Basin area, top:	53-1/2" x 32-1/8" (1359 mm x 816 mm)
Weight:	110 lbs (49.9 kg)
Minimum floor load:	35 lbs/ft² (170.9 kg/m²)
Water depth:	15" (381 mm)
Water capacity:	57 gal (215.8 L)
Template:	Drop-in, 1042556-7, required, included
Electrical component	Pump: 120 V, 7.5 A, 60 Hz
rating:	
Pump speed:	Single

#### Notes

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

Kit is required for under-mount installations (sold separately).

The suction line extends 4-5/8" (117 mm) beyond the edge of the rim. The pump base extends 1/8" (3 mm) beyond the edge of the rim. Modify the framing as needed.

