# Preston Technical Specification Robe Hook DN8403


## **Stock Numbers:**

- q DN8403PB Robe Hook Polished Brass Finish Concealed Screw Mounting
- q DN8403CH Robe Hook Polished Chrome Finish Concealed Screw Mounting
- q DN8403MPW Robe Hook Matte Pewter Finish Concealed Screw Mounting
- DN8403BN Robe Hook Brushed Nickel Finish Concealed Screw Mounting

#### **Materials:**

**Robe Hook** is die cast from highest quality zinc alloy (zamac). Castings are triple plated with a polished brass, polished chrome, or matte pewter finish.

#### **Dimensions:**



### **Installation Instructions:**

- 1. Position the mounting plate on the wall at desired location with "UP" facing you.
- One at a time, place each anchor screw through the mounting plate, centered in each large hole. Using a Phillips screwdriver, turn the anchor screw while applying pressure. Screw will self drill and tap into drywall. Do not over tighten.
- 3. Place assembly over the mounting post, setscrew facing down.
- 4. Tighten setscrew.

## **Cleaning Instructions:**

To preserve the fine finish of this product, clean only with a soft damp cloth. Dry well. Do not use commercial or abrasive cleaners.

Stock Number:	Robe Hook
By CSI Bath Furnishings	



25300 AL MOEN DRIVE • NORTH OLMSTED, OH 44070 (800) 321-8809 • FAX: (800) 848-6636 • INTERNATIONAL: (440) 962-2000 • FAX: (440) 962-2726 CUSTOMER SERVICE (USA): 800-882-0116 ©Copyright CSI Bath Furnishing Division of Moen 02/22/01 Literature #BA1045