
spirax sarco

TI-P164-02 CMGT Issue 9

Fig 12 **Brass and Bronze Strainers**



The Fig $1\dot{2}$ is a brass and bronze screwed Y-type strainer. The standard stainless steel screen is 0.8 mm perforations. As options, other perforations and mesh sizes are available as well as monel screens. The strainer cap can be drilled and tapped for blowdown and drain valves if required.

Standards

This product fully complies with the requirements of the Pressure Equipment Directive (PED) and carry the 🕻 🕻 mark when so required.

This product is available with a manufacturer's Typical Test Report for the body and cap.

Note: All certifications/inspections requirements must be stated at the time of order placement.

Sizes and pipe connections


Fig 12 Brass 3/8'

Fig 12 Bronze 1/2", 3/4", 1", 11/4", 11/2", 2" and 21/2" Connections: Screwed BSP (BS 21) or NPT

Optional extras

	Stainless steel	Perforations	1.6, 3.0 mm	
Strainer screens	Stainless steel	Mesh	40, 100, 200	
Strainer screens	Manal	Perforations	0.8, 3.0 mm	
	Monel	Mesh	100	
	Strainer size	Blowdown valve	Drain valve	
Blowdown or drain valve connections	3/8" and ½"	1/4"	1/4"	
The cap can be drilled to the following sizes to enable a blowdown or drain valve to be fitted at extra cost.	3/4" and 1"	1/2"	1/2"	
	1¼" and 1½"	1"	3/4"	
	2" and 2½"	11/4"	3/4"	

Pressure/temperature limits




The product **must not** be used in this region.

Body	PN25	
РМА	Maximum allowable pressure	25 bar g
TMA	Maximum allowable temperature	210 °C
Minim	-198 °C	
*PMO	Maximum operating pressure for saturated steam service	
Desig	38 bar g	

Materials

No.	Part		Material	
1	Body	3/8"	Brass	EN 12165 CW617N
		½" to 2½"	Bronze	EN 1982 CC491K
2	Сар		Brass	EN 12165 CW617N
3	Cap gasket		Reinforced exfoliated	d graphite
4	Strainer screen		Stainless steel	ASTM A240 316 L



K, values

Size	3/8"	1/2"	3/4"	1"	11/4"	11/2"	2"	21/2"
Perforations 0.8, 1.6 and 3 mm	2.6	3	6.2	11.3	26	41	68	98
Mesh 40 and 100	2.6	3	6.2	11.3	26	41	68	98
Mesh 200	2.6	3	6.2	9.3	21	33	55	78


For conversion:

 $C_v(UK) = K_v \times 0.963$

 $C_{v}^{v}(US) = K_{v}^{v} \times 1.156$

Dimensions/weights (approximate) in mm and kg Brass body

Size	Α	В	С	D	Screening area cm ²	Weight
3/8"	69	50	80	24 A/F	27	0.45
Bronze body						
1/2"	72	54	85	30 A/F	27	0.55
3/4"	82	64	110	36 A/F	43	0.70
1"	104	72	130	46 A/F	73	1.00
11/4"	138	100	170	52 A/F	135	1.60
11/2"	150	110	190	60 A/F	164	2.10
2"	178	133	212	79 A/F	251	4.80
2½"	207	152	240	98 A/F	327	7.70
			,			



Safety information, installation and maintenance

For full details see the Installation and Maintenance Instructions (IM-S26-01-EN-ISS1) supplied with the product.

Installation note:

Suitable isolation valves must be installed to allow for safe maintenance and trap replacement. We also recommend that a Spirax Sarco DV depressurisation type valve (see the product specific TI literature for further details) be installed to ensure that any pressure is isolated and safely vented to atmospheric pressure before attempting to maintain the strainer.

Maintenance note:

Maintenance can be completed with the strainer in the pipeline, once the safety procedures have been observed. It is recommended that a new gasket is used whenever maintenance is undertaken.

Disposal

The product is recyclable. No ecological hazard is anticipated with disposal of this product, providing due care is taken.

How to order

Example: 1 off Spirax Sarco 11/2" Fig 12 bronze strainer with screwed BSP connections and stainless steel screen having 0.8 mm perforations.

Spare parts

The spare parts available are shown in solid outline. Parts drawn in a grey line are not supplied as spares.

Available spares

Strainer screen (state material, size of perforation or mesh and size of strainer)	4
Cap gasket (packet of 3)	3

How to order spares

Always order spares by using the description given in the column headed 'Available spares' and state the size and type of strainer and perforations or mesh required.

Example: 1 - Stainless steel strainer screen having 0.8 mm perforations for a 3/4" Spirax Sarco Fig 12 strainer.

Fig 12 Sizes ½" to 1"





Fig 12 Sizes 3/8" and 11/4" to 21/2"



Recommended tightening torques

				<u> </u>	
Item	Size	Qty		or mm	N m
	3/8"	1	22 A/F	M28	35 - 40
	1/2"	1	22 A/F	M28	35 - 40
	3/4"	1	27 A/F	M32	42 - 48
2	1"	1	27 A/F	M42	70 - 80
2	11/4"	1	41 A/F	M56	124 - 144
	11/2"	1	41 A/F	M60	164 - 184
	2"	1	55 A/F	M72	234 - 264
	2½"	1	55 A/F	31/4"-16 UNS	300 - 330
5	3"	6	3⁄4" A/F	7/16" UNF x 1½" (38 mm)	50 - 55