

# Quick-Acting Tubing Cutters

Models 151-156

## Features

Models 151-156 feature a quick-acting design, I-beam construction, hardened wear surfaces and thrust bearing slide assemblies for smooth operation.

All Models now include an X-CEL® Knob and X-CEL Pin for quicker cutting and wheel replacement.

These cutters are available in models for plastic pipe or metallic tubing.

Models 151 and 152 feature fold-away reamers.



## X-CEL Means Speed

Many of our most popular tubing cutters now include several X-CEL features to make your job quicker and easier.

X-CEL Knob – cut tubing more quickly and easily with our larger, more ergonomic designs.

X-CEL Wheel Pin – change your cutter wheel quickly using our new ball detent design...no tool needed...no lost clips!

Spare cutter wheels included for maximum uptime.



**1** **QUICKER CUT!** Bigger, better knob allows you to cut tubing more quickly!

**2** **QUICKER WHEEL CHANGE** Unique wheel pin-no tool needed...no lost clips...

change to cut copper or plastic in seconds!

**3 SPARE WHEEL INCLUDED!**

**4 TOUGHER THAN EVER!** Reinforced components. Your new RIDGID Quick-Acting Cutter will last longer than ever.

## Ordering Information

Cat. No.	Model No.	Description	Std. Wheel	Capacity		Weight		Std. Pack
				in.	mm	lb.	kg	
31632	151	Quick-Acting Cutter	E-3469	1/4-1 5/8	6-42	1 1/4	0.4	6
31637	151-P	Above w/Wheel For Plastic	E-2155	1/8-1 1/4**	10-40**	1 1/4	0.4	6
31642	152	Quick-Acting Cutter	E-3469	1/4-2 5/8	6-66	2	0.9	1
31647	152-P	Above w/Wheel For Plastic	E-2155	1/4-2**	10-63**	2	0.9	1
34572	152-P	Above w/Wheel For PVC	E-5272	1/4-2**	10-63**	2	0.9	1
36597	153	Quick-Acting Cutter	E-3469	1 1/4-3 1/2	32-90	2	0.9	1
36592	153-P	Above w/Wheel For Plastic*	E-2155	1-3**	25-75**	2	0.9	1
31652	154	Quick-Acting Cutter	E-2558	1 7/8-4 1/2	48-116	3 7/8	1.4	1
31657	154-P	Above w/Wheel For Plastic*	E-2156	1 1/2-4**	50-110**	3 7/8	1.4	1
31662	156	Quick-Acting Cutter	E-2558	4-6 5/8	100-170	5	1.9	1
31667	156-P	Above w/Wheel For Plastic*	E-2157	4-6**	110-160**	5	1.9	1

\* Plastic models do not include spare cutting wheels  
 \*\*Nominal Plastic Pipe Size

**RIDGID Quick-Acting plastic cutter models are equipped to easily convert to cut copper or other metallic tubing.**

1. Remove spare copper cutting wheel from knob.
2. Reverse knob position so that the "Cu" notation is visible inside the knob.
3. Screw knob back on to handle.
4. Using the X-CEL Wheel Pin, you can quickly replace the existing plastic cutting wheel with the copper cutting wheel. You're now ready to cut copper, aluminum, and brass tubing.
5. When you wish to revert to plastic cutting, follow the same instructions but make sure to reposition knob so that "PE" and "PVC" notations are visible inside knob.

