## **Recessed Fixtures Technical Specification**

## **Recessed Paper Holder w/ Clamp**

# **DN5075**

## **Stock Numbers:**

## **Dimensions:**

6.25\*

- DN5075 Recessed Paper Holder w/ Clamp
- DN5075W Recessed Paper Holder w/Clamp **Glacier Finish**





## **Installation Instructions:**

- 1. Cut a square hole into wall measuring  $5\frac{1}{4}$  x  $5\frac{1}{4}$ .
- 2. Loosely attach both screws through the recess item into the slots on the clamp.
- 3. Slide the wall clamp through the wall opening angling it through the opening if necessary.
- 4. Position the recess item until flush with the wall and tighten both screws.

## **Cleaning Instructions:**

To preserve the fine finish of this product, clean only with a soft damp cloth. Dry well. Do not use commercial or abrasive cleaners.

Stock Number:

Recessed

Paper Holder By Creative Specialties

25300 AL MOEN DRIVE . NORTH OLMSTED, OH 44070 CORPORATE HEADQUARTERS: (800) 321-8809 • FAX: (800) 848-6636 INTERNATIONAL: (440) 962-2000 • FAX: (440) 962-2726 CUSTOMER SERVICE (USA): 800-882-0116 • FAX: (888) 379-2720 WWW.MOEN.COM ©Copyright Creative Specialties International Literature #BA1697

## **Materials:**

Recessed Paper Holder shell is stamped from a special alloy brass strip

and finished with a triple plated polished chrome finish with a lacquer coat for added protection. Roller is plastic and spring loaded. Installation C-Clamp is stamped

from

type 304 steel.

