

Water Connects Us™



Electronic Gooseneck Hand Washing Faucet



Description

120 VAC/6.75 VDC Line Powered, Sensor Activated, Electronic Hand Washing Faucet for pre-tempered or hot and cold water operation.

120 VAC/6.75 VDC Plug-in Adapter Powered Models with Voltage Adapter (-P)

☐ EAF-700-P Single Supply Faucet (For pre-mixed water only)

☐ EAF-700-P-ISM With Integral Spout Temperature Mixer

120 VAC/6.75 VDC Plug-in Adapter Powered Models Less Voltage Adapter (-LT) (EAF-44 power splitter included, must order adapter separately)

☐ EAF-700-LT Single Supply Faucet (For pre-mixed water only)

☐ EAF-700-LT-ISM With Integral Spout Temperature Mixer

Flow Rate

☐ 1.5 gpm/5.7 Lpm Laminar Flow Spray Insert

Specifications

Sensor Activated, Electronic, Chrome Plated Die-Cast Metal, Gooseneck Hand Washing Faucet with the following features:

- Temporary-off Feature for Cleaning
- 12/24 hour Hygienic Rinse Line Purge Function Field Settable
- Unitary Spout Housing Assembly for Easy Cleaning
- Modular One-piece Construction with all Concealed Components above deck
- Double Infrared Sensors with Automatic Setting Feature and Microprocessor
- Bi-stable Magnetic Solenoid Valve
- Water Supply Connection with Flexible High-pressure Hose and Strainer
- 120 VAC/6.75 VDC Plug-in Adapter (must be ordered separately for Less Adapter (-LT) faucets)
- Appropriate Mounting Hardware included

Variations

□ ISM	Integral Spout Mixer
□ LT	Less Adapter (includes EAF-44 Power Splitter)

Accessories

Trim Plates

☐ SFP-11 Trim Plate for 4" (102 mm) Centerset Sink ☐ SFP-22 Trim Plate for 8" (204 mm) Centerset Sink Trim Plates must be specified and ordered separately

Spray Inserts

☐ 1.5 gpm/5.7 Lpm Aerated Stream

Voltage Adapters

■ EAF-11	6 VDC Plug-in Adapter, US	
☐ EAF-37	6 VDC Box Mount Adapter	
☐ EAF-41	European Plug-in Adapter	
■ EAF-39	United Kingdom Plug-in Adapter	
- · · · - · · · · · · · · · · · · · · ·		

Extension Cables

- ☐ **EAF-24-A** 11-13/16" (300 mm) Extension Cable ☐ **EAF-25-A** 47 ¼" (1200 mm) Extension Cable ☐ EAF-17-A 126" (3200 mm) Extension Cable
- Power Splitter
 - □ EAF-44 Power Splitter

Warranty

3 year (limited)

Compliant to: ASME A112.18.1-2005



The new Optima i.q. faucet Bringing intelligence to water

Sloan's new Optima £q. EAF-700 Series electronic hand washing faucets operate by means of a dual infrared sensor and microprocessor based logic. The modular design incorporates all of the operating components of the faucet, including the sensor, solenoid and circuitry above the sink within a

ISM models feature an integral temperature control lever which allows the user to adjust the water temperature. This adjustment can also be converted to a fixed setting. EAF faucets ordered without the ISM variation must be connected to a single, pre-tempered water supply.

The i.q.-Click feature allows the user to place the faucet into optional function modes, including "continuous run" and "temporary off" simply by pressing a button on the spout. The use of the **i.q.-Click** feature is recommended only in installations where users have a regular familiarity with the faucet.

Optima La. EAF-700 series faucets are powered by a 120 VAC/ 6.75 VDC plug-in voltage adapter. Each adapter can supply power for up to six (6) faucets by means of the Power Splitter (optional) with each (-LT) faucet.







This space for Architect/Engineer approval				
Job Name	Date			
Model Specified	Quantity			
Variations Specified				
Customer/Wholesaler				
Contractor				
Architect				



Description

120 VAC/6.75 VDC Line Powered, Sensor Activated, Electronic Gooseneck Hand Washing Faucet for pre-tempered or hot and cold water operation.

Flow Rate

☐ 1.5 gpm/5.7 Lpm Laminar Flow Spray Insert

ELECTRICAL SPECIFICATIONS

Control Circuit

6.75 VDC - Includes Auto Set Range Adjustment

Sensor Range Nominal: 4"-7" (102 mm-179 mm)

Faucet Adaptive Selfadjustment Range:

2"-14" (51 mm -356 mm) nominal


Power Supply

120 VAC/6.75 VDC Plug-in Voltage Adapter

Time Out Setting

2 minutes — Maximum time faucet will run upon continuous detection (except for i.q.-Click models that are otherwise set in continuous run).

ELECTRICAL CONNECTION FOR UP TO SIX (6) FAUCETS USING ONE (1) ADAPTER



10-1/32" (255 mm) 5-7/8 (147 mm) 3-15/16 (100 mm)5-11/32' (151 mm) 2-9/16 2-1/4" (57 mm) (65 mm)

î.q.-Click FEATURE

The i.q.-Click is a button that extends from the underside of the faucet spout that allows the user to place the faucet into the following function modes: Continuous Run, Temporary Off, Permanent Off and Auto Set Range Adjustment.

Because the use of the i.q.-Click feature requires familiarity with the faucet, this feature is not recommended for faucets intended for use by the general public. The i.q.-Click is ideal for use in hospital rooms, executive rest rooms and other locations where the primary user has regular contact with the product.

1.q.-Click SETTINGS


Function	Press Button	LED Signal		
Continuous Run — 2 minute default setting (adjustable from 1 - 20 minutes)	1 time for 2 seconds	5 short flashes		
reset:	1 time or will reset automatically after 2 minutes			
Temporary Off	2 times (double click)	5 short flashes followed by periodic flashing		
reset:	1 time or will reset automatically after 2 minutes			
Auto Set Range Adjustment	2 times (double click) and then 1 time for 5 seconds	5 short flashes followed by 4 short flashes		

OPERATION


As the user's hands enter the beam's effective range, the beam is reflected back into the sensor receiver and activates the solenoid valve allowing water to flow from the faucet. Water will flow until the hands are removed or until the faucet reaches its automatic time out limit setting.

ROUGH-IN

EAF-700 Faucets with Single Line Water Supply



EAF-700-ISM **Faucets with Hot and Cold Water Supply**



When the EAF faucet is installed on a sink that has three (3) hole punchings, a Trim Plate sho uld be used. Trim Plates must be specified and ordered separately:

SFP-11

Trim Plate for 4" (102 mm) Centerset Sink

SFP-22

Trim Plate for 8" (204 mm) Centerset Sink

SLOAN • 10500 SEYMOUR AVENUE • FRANKLIN PARK, IL 60131

Phone: 1-800-982-5839 or 1-847-671-4300 • Fax: 1-800-447-8329 or 1-847-671-4380 • www.sloanvalve.com