

Brass Barb Fittings

Use: For use with plastic or rubber tubing. Installation requires a hose clamp.

Design Features

- · Manufactured with dryseal pipe threads
- · Available in a broad range of sizes
- · Compatible with ANSF B1.20.1
- · Low lead compliant





Operating Specifications

| Temperature: | -40° – 160° F | |
|-------------------|-----------------|--|
| Working Pressure: | 150 PSI maximum | |

| Fitting Material Specifications | |
|---------------------------------|--------------------|
| Body | Low Lead Compliant |
| Nut (if applicable) Brass | |

| Sku | Description |
|-----------|---|
| PFXMHBABN | Male Hose Barb Adaptor 1/8" ID Hose Barb x 1/4" MIP |
| PFXMHBBAN | Male Hose Barb Adaptor 1/4" ID Hose Barb x 1/8" MIP |
| PFXFHBBBN | Female Hose Barb Adaptor 1/4" ID Hose Barb x 1/4" FIP |
| PFXMHBBBN | Male Hose Barb Adaptor 1/4" ID Hose Barb x 1/4" MIP |
| PFXMHBBCN | Male Hose Barb Adaptor 1/4" ID Hose Barb x 3/8" MIP |
| PFXMHBBDN | Male Hose Barb Adaptor 1/4" ID Hose Barb x 1/2" MIP |
| PFXMHBCBN | Male Hose Barb Adaptor 3/8" ID Hose Barb x 1/4" MIP |
| PFXFHBCCN | Female Hose Barb Adaptor 3/8" ID Hose Barb x 3/8" FIP |

| Sku | Description |
|-----------|---|
| PFXMHBCCN | Male Hose Barb Adaptor 3/8" ID Hose Barb x 3/8" MIP |
| PFXMHBCDN | Male Hose Barb Adaptor 3/8" ID Hose Barb x 1/2" MIP |
| PFXMHBDCN | Male Hose Barb Adaptor 1/2" ID Hose Barb x 3/8" MIP |
| PFXMHBDDN | Male Hose Barb Adaptor 1/2" ID Hose Barb x 1/2" MIP |
| PFXMHBDFN | Male Hose Barb Adaptor 1/2" ID Hose Barb x 3/4" MIP |
| PFXMHBEFN | Male Hose Barb Adaptor 5/8" ID Hose Barb x 3/4" MIP |
| PFXMHBFDN | Male Hose Barb Adaptor 3/4" ID Hose Barb x 1/2" MIP |
| PFXMHBGGN | Male Hose Barb Adaptor 1" ID Hose Barb x 1" MIP |

Listings & Certifications

Low Lead Compliant CSA certified to NSF/ANSI 372 - Drinking water system components - Lead Content, and conforms to the requirements for "lead free" plumbing products as defined by California, Vermont, Maryland, and Louisiana state law and by Section 1417 of the US Safe Drinking Water Act.





Brass Compression Fittings

Use: For use with potable water, instrumentation, hydraulic, and pneumatic systems. Designed for use with aluminum, copper, and plastic tubing. Not intended for use with steel tubing.

Design Features

- \cdot Little to no tube preparation. Compression fittings do not require flaring, soldering, or other types of tube preparation
- · Compatible with SAEJ512

Operating Specifications

| Temperature: | -65° – 25 |
|-------------------|-------------|
| Working Pressure: | See chart |
| Vibration: | Fair vibrat |

5° – 250° F at maximum operating pressures e chart below ir vibration resistance

| Fitting Material Specifications | |
|---------------------------------|--------------------|
| Body | Low Lead Compliant |
| Compression Sleeve | Brass |
| Compression Nut Brass | |



| | Working Pressure | |
|-----|------------------|--------------------|
| PSI | Tube OD (Inches) | Tube Wall (Inches) |
| 400 | 1/8 | 0.030 |
| 400 | 3/16 | 0.030 |
| 300 | 1/4 | 0.030 |
| 300 | 5/16 | 0.032 |
| 200 | 3/8 | 0.032 |
| 200 | 1/2 | 0.032 |
| 150 | 5/8 | 0.035 |
| 100 | 3/4 | 0.035 |
| 75 | 7/8 | 0.035 |

| Sku | Description |
|-----------|---|
| PFCSAN | Sleeve For 1/8" OD Tube |
| PFPCSBN | Plastic Sleeve For 1/4" OD Tube |
| PFPCSDN | Plastic Sleeve For 1/2" OD Tube |
| PFPCSCN | Plastic Sleeve For 3/8" OD Tube |
| PFPCSEN | Plastic Sleeve For 5/8" OD Tube |
| PFCNAN | Nut For 1/8" OD Tube |
| PFCNDNN | Nut For 1/2" OD Tube |
| PFCNEN | Compression Nut For 5/8" OD Tube |
| PFXBRIDN | Brass Insert For 1/2" OD Tube |
| PFXBRIEN | Brass Insert For 5/8" OD Tube |
| PFXCCBN | Cap 1/4" OD Tube |
| PFXCCCN | Cap 3/8" OD Tube |
| PFXCPCN | Plug For 3/8" OD Tube |
| PFXMCUAAN | Male Adaptor 1/8" OD Tube x 1/8" MIP |
| PFXMCUBAN | Male Reducing Adaptor 1/4" OD Tube x 1/8" MIP |
| PFXMCUBBN | Male Adaptor 1/4" OD Tube x 1/4" MIP |

| Sku | Description |
|-----------|---|
| PFCSBN | Sleeve For 1/4" OD Tube |
| PFCSDN | Sleeve For 1/2" OD Tube |
| PFCSCN | Sleeve For 3/8" OD Tube |
| PFCSEN | Sleeve For 5/8" OD Tube |
| PFCS78N | Sleeve For 7/8" OD Tube |
| PFCNBN | Nut For 1/4" OD Tube |
| PFCNCNN | Nut For 3/8" OD Tube |
| PFXBRIBN | Brass Insert For 1/4" OD Tube |
| PFXBRICN | Brass Insert For 3/8" OD Tube |
| PFXSSIEN | Stainless Steel Insert For 5/8" OD Tube |
| PFXCCDN | Cap 1/2" OD Tube |
| PFXCCEN | Cap 5/8" OD Tube |
| PFXLNPCN | Lav Nose Piece |
| PFXFCUBAN | Female Reducing Adaptor 1/4" OD Tube x 1/8" FIP |
| PFXFCUBBN | Female Adaptor 1/4" OD Tube x 1/4" FIP |
| PFXFCUBCN | Female Reducing Adaptor 1/4" OD Tube x 3/8" FIP |



Brass Compression Fittings

| Sku | Description |
|-------------|--|
| PFXMCUBCN | Male Reducing Adaptor 1/4" OD Tube x 3/8" MIP |
| PFXMCUBDN | Male Reducing Adaptor 1/4" OD Tube x 1/2" MIP |
| PFXCARBDBN | Sweat Reducing Adaptor 1/2" Nominal Sweat x 1/4" OD Tube |
| PFXMCUDDN | Male Adaptor 1/2" OD Tube x 1/2" MIP |
| PFXMCADCCPN | Male Reducing Adaptor 3/8" OD Tube x 1/2" MIP |
| PFXMCRADCN | Male Reducing Adaptor 1/2" OD Tube x 3/8" MIP |
| PFXMCUCAN | Male Reducing Adaptor 3/8" OD Tube x 1/8" MIP |
| PFXMCUCBCP | Male Reducing Adaptor 3/8" OD Tube x 1/4" MIP |
| PFXFCUCDN | Female Reducing Adaptor 3/8" OD Tube x 1/2" FIP |
| PFXFCUCDCPN | Female Reducing Adaptor 3/8" OD Tube x 1/2" FIP |
| PFXFCUCCN | Female Adaptor 3/8" OD Tube x 3/8" FIP |
| PFXMCUCPCCN | Male Adaptor 3/8" OD Tube x 3/8" MIP |
| PFXMCACCCPN | Adaptor 3/8" OD Tube x 3/8" MIP |
| PFXFCUECN | Female Reducing Adaptor 5/8" OD Tube x 3/8" FIP |
| PFXFCUEDN | Female Reducing Adaptor 5/8" OD Tube x 1/2" FIP |
| PFXMCUEFN | Male Reducing Adaptor 5/8" OD Tube x 3/4" MIP |
| PFXMCU78FN | Male Reducing Adaptor 7/8" OD Tube x 3/4" MIP |
| PFXMCEBAN | Male Reducing Elbow Adaptor 1/4" OD Tube x 1/8" MIP |
| PFXMCEBBN | Male Elbow Adaptor 1/4" OD Tube x 1/4" MIP |
| PFXMCEDCN | Male Reducing Elbow Adaptor 1/2" OD Tube x 3/8" MIP |
| PFXCEDDN | Union Elbow 1/2" OD Tube x 1/2" OD Tube |
| PFXMCECBN | Male Reducing Elbow Adaptor 3/8" OD Tube x 1/4" MIP |
| PFXMCECCN | Male Elbow Adaptor 3/8" OD Tube x 3/8" MIP |
| PFXFCECDN | Female Elbow Reducing Adaptor 3/8" OD Tube x 1/2" FIP |
| PFXMCECDN | Male Reducing Elbow Adaptor 3/8" OD Tube x 1/2" MIP |
| PFXCEECCPN | Reducing Union Elbow 5/8" OD Tube x 3/8" OD Tube |
| PFXCEEEN | Union Elbow 5/8" OD Tube x 5/8" OD Tube |
| PFXCUDCN | Reducing Union 1/2" OD Tube x 3/8" OD Tube |
| PFXCUCBN | Reducing Union 3/8" OD Tube x 1/4" OD Tube |
| PFXCUBECPCN | Union 3/8" OD Tube x 3/8" OD Tube |
| PFXCUECN | Reducing Union 5/8" OD Tube x 3/8" OD Tube |
| PFXCCUEN | Union 5/8" OD Tube x 5/8" OD Tube |
| PFXCUACCN | Flare Compression Adaptor 3/8" Female Flare x 3/8" OD Tube |
| PFXCTDN | Tee 1/2" OD Tube x 1/2" OD Tube x 1/2" OD Tube |
| PFXCTCCBN | Reducing Tee 3/8" OD Tube x 3/8" OD Tube x 1/4" OD Tube |
| PFXCTCN | Tee 3/8" OD Tube x 3/8" OD Tube x 3/8" OD Tube |
| PFXCTEN | Tee 5/8" OD Tube x 5/8" OD Tube x 5/8" OD Tube |

| Sku | Description |
|-------------|--|
| PFXFCUBDN | Female Reducing Adaptor 1/4" OD Tube x 1/2" FIP |
| PFXMCUDBN | Male Reducing Adaptor 1/2" OD Tube x 1/4" MIP |
| PFXFCUDDN | Female Adaptor 1/2" OD Tube x 1/2" FIP |
| PFXFCUDCN | Female Reducing Adaptor 1/2" OD Tube x 3/8" FIP |
| PFXARBDCN | Compression Sweat Adaptor 1/2" Nominal Sweat x 3/8" OD Tube |
| PFXMCUDFN | Male Reducing Adaptor 1/2" OD Tube x 3/4" MIP |
| PFXFCUCBN | Female Reducing Adaptor 3/8" OD Tube x 1/4" FIP |
| PFXMCUCBN | Male Reducing Adaptor 3/8" OD Tube x 1/4" MIP |
| PFXMCUCDN | Male Reducing Adaptor 3/8" OD Tube x 1/2" MIP |
| PFXMCUCDCPN | Male Reducing Adaptor 3/8" OD Tube x 1/2" MIP |
| PFXMCUCCN | Male Adaptor 3/8" OD Tube x 3/8" MIP |
| PFXFCACCCPN | Adaptor 3/8" OD Tube x 3/8" FIP |
| PFXMCUCFN | Male Reducing Adaptor 3/8" OD Tube x 3/4" MIP |
| PFXMCUECN | Male Reducing Adaptor 5/8" OD Tube x 3/8" MIP |
| PFXMCUEDN | Male Reducing Adaptor 5/8" OD Tube x 1/2" MIP |
| PFXFCU78FN | Female Reducing Adaptor 7/8" OD Tube x 3/4" FIP |
| PFXMCU78GN | Male Reducing Adaptor 7/8" OD Tube x 1" MIP |
| PFXCEBBN | Union Elbow 1/4" OD Tube x 1/4" OD Tube |
| PFXMCEBCN | Male Reducing Elbow Adaptor 1/4" OD Tube x 3/8" MIP |
| PFXMCEDDN | Male Elbow Adaptor 1/2" OD Tube x 1/2" MIP |
| PFXMCECAN | Male Reducing Elbow Adaptor 3/8" OD Tube x 1/8" MIP |
| PFXFCECCN | Female Elbow Adaptor 3/8" OD Tube x 3/8" FIP |
| PFXCECCN | Union Elbow 3/8" OD Tube x 3/8" OD Tube |
| PFXFCECPCDN | Female Elbow Reducing Adaptor 3/8" OD Tube x 1/2" FIP |
| PFXCEECN | Reducing Union Elbow 5/8" OD Tube x 3/8" OD Tube |
| PFXMCEEDN | Male Reducing Elbow Adaptor 5/8" OD Tube x 1/2" MIP |
| PFXCUBN | Union 1/4" OD Tube x 1/4" OD Tube |
| PFXCUDN | Union 1/2" OD Tube x 1/2" OD Tube |
| PFXCUCN | Union 3/8" OD Tube x 3/8" OD Tube |
| PFXCUEDN | Reducing Union 5/8" OD Tube x 1/2" OD Tube |
| PFXCUECCPN | Reducing Union 5/8" OD Tube x 3/8" OD Tube |
| PFXCU78N | Union 7/8" OD Tube x 7/8" OD Tube |
| PFXCTBN | Tee 1/4" OD Tube x 1/4" OD Tube x 1/4" OD Tube |
| PFXCTFCCBN | Female Tee Adaptor 3/8" OD Female x 3/8" OD Tube x 1/4" OD Tube |
| PFXCTFCCCN | Female Tee Adaptor 3/8" OD Female x 3/8" OD Tube x 3/8" OD Tube |
| PFXCTCCPN | Tee 3/8" OD Tube x 3/8" OD Tube x 3/8" OD Tube |

Listings & Certifications

Low Lead Compliant CSA certified to NSF/ANSI 372 – Drinking water system components – Lead Content, and conforms to the requirements for "lead free" plumbing products as defined by California, Vermont, Maryland, and Louisiana state law and by Section 1417 of the US Safe Drinking Water Act.







Brass Flare Fittings

Use: For use with fuel, oil, liquefied petroleum (LP), and natural gas lines. Designed for use with aluminum, copper, brass, and welded steel tubing that can be flared.

Design Features

- \cdot Recommended for higher pressures than those covered by compression fittings
- · Resist mechanical pull-out
- · Compatible with SAEL512 or SAEJ513

Operating Specifications

| Temperature: | -65° – 250° F at maximum operating pressures |
|--|--|
| Working Pressure: | See chart below |
| Vibration: | Good vibration resistance* |
| *Recommend long flare nuts when greater vibration resistance is required | |

| Fitting Material Specifications | | |
|---------------------------------|-------|--|
| Body | Brass | |

| Sku | Description |
|----------|---|
| PFFCB | Cap 1/4" OD Tube |
| PFFCD | Cap 1/2" OD Tube |
| PFFCE | Cap 5/8" OD Tube |
| PFFPD | Plug 1/2" OD Tube |
| PFFTD | Tee 1/2" OD Tube x 1/2" OD Tube x 1/2" OD Tube |
| PFMFECB | Male Reducing Elbow Adaptor 3/8" OD Tube x 1/4" MIP |
| PFMFECC | Male Elbow 3/8" OD Tube x 3/8" MIP |
| PFMFEDC | Male Reducing Elbow Adaptor 1/2" OD Tube x 3/8" MIP |
| PFMFEED | Male Reducing Elbow Adaptor 5/8" OD Tube x 1/2" MIP |
| PFFUB | Union 1/4" OD Tube x 1/4" OD Tube |
| PFMFUBB | Male Adaptor 1/4" OD Tube x 1/4" MIP |
| PFMFUBD | Male Reducing Adaptor 1/4" OD Tube x 1/2" MIP |
| PFMFUCA | Male Reducing Adaptor 3/8" OD Tube x 1/8" MIP |
| PFMFUCB | Male Reducing Adaptor 3/8" OD Tube x 1/4" MIP |
| PFMFUCC | Male Adaptor 3/8" OD Tube x 3/8" MIP |
| PFMFUCD | Male Reducing Adaptor 3/8" OD Tube x 1/2" MIP |
| PFMFUCF | Male Reducing Adaptor 3/8" OD Tube x 3/4" MIP |
| PFMFUDB | Male Reducing Adaptor 1/2" OD Tube x 1/4" MIP |
| PFFFUDD | Female Adaptor 1/2" OD Tube x 1/2" FIP |
| PFMUSTLD | Steel Adaptor 1/2" OD Tube x 1/2" MIP |

| Sku | Description |
|-----------|---|
| PFFCC | Cap 3/8" OD Tube |
| PFFCEFT | Cap 5/8" OD (15/16-16 Thread) |
| PFFPC | Plug 3/8" OD Tube |
| PFFTC | Tee 3/8" OD Tube x 3/8" OD Tube x 3/8" OD Tube |
| PFMFEBB | Male Elbow Adaptor 1/4" OD Tube x 1/4" MIP |
| PFMBRFECC | Male Elbow Adaptor 3/8" OD Tube x 3/8" MIP |
| PFMFECD | Male Reducing Elbow Adaptor 3/8" OD Tube x 1/2" MIP |
| PFMBRFEDD | Male Elbow Adaptor 1/2" OD Tube x 1/2" MIP |
| PFMFEFF | Male Elbow 3/4" OD Tube x 3/4" MIP |
| PFMFUBA | Male Reducing Adaptor 1/4" OD Tube x 1/8" MIP |
| PFMFUBC | Male Reducing Adaptor 1/4" OD Tube x 3/8" MIP |
| PFFUC | Union 3/8" OD Tube x 3/8" OD Tube |
| PFFFUCB | Female Reducing Adaptor 3/8" OD Tube x 1/4" FIP |
| PFFFUCC | Female Adaptor 3/8" OD Tube x 3/8" FIP |
| PFFFUCD | Female Reducing Adaptor 3/8" OD Tube x 1/2" FIP |
| PFFUCD | Reducing Union 1/2" OD Tube x 3/8" OD Tube |
| PFFUD | Union 1/2" OD Tube x 1/2" OD Tube |
| PFMFUDC | Male Reducing Adaptor 1/2" OD Tube x 3/8" MIP |
| PFMFUDD | Male Adaptor 1/2" OD Tube x 1/2" MIP |
| PFFFUDF | Female Reducing Adaptor 1/2" OD Tube x 3/4" FIP |





Brass Flare Fittings

| PFMFUDF | Male Reducing Adaptor 1/2" OD Tube x 3/4" MIP |
|----------|--|
| PFFUE | Union 5/8" OD Tube x 5/8" OD Tube |
| PFOMFUED | Male Reducing Adaptor 5/8" OD Tube x 1/2" MIP |
| PFOMFUEF | Male Reducing Adaptor 5/8" OD Tube x 3/4" MIP |
| PFMFU78F | Male Reducing Adaptor 7/8" OD Tube x 3/4" MIP |
| PFSFNC | Short Nut 3/8" OD Tube |
| PFSFNE | Short Nut 5/8" OD Tube |
| PFSFN78 | Short Nut 7/8" OD Tube |
| PFSNVCD | Swivel Nut Valve Connector 1/2" OD Tube x 1/2" OD Tube |
| PFSRFNFC | Short Refrigeration Flare Nut Forged 3/8" OD Tube |
| PFSRFNFE | Short Refrigeration Flare Nut Forged 5/8" OD Tube |

| PFFFU516B | Female Reducing Adaptor 5/16" OD Tube x 1/4" FIP |
|-----------|--|
| PFOFFUED | Female Reducing Adaptor 5/8" OD Tube x 1/2" FIP |
| PFFUED | Reducing Union 5/8" OD Tube x 1/2" OD Tube |
| PFMFUFF | Male Adaptor 3/4" OD Tube x 3/4" MIP |
| PFSFNB | Short Nut 1/4" OD Tube |
| PFSFND | Short Nut 1/2 OD Tube |
| PFSFNF | Short Nut 3/4" OD Tube |
| PFSNVCC | Swivel Nut Valve Connector 3/8" OD Tube x 3/8" OD Tube |
| PFFSRFNB | Short Refrigeration Flare Nut Forged 1/4" OD Tube |
| PFSRFNFD | Short Refrigeration Flare Nut Forged 1/2" OD Tube |

| | | | | MA | XIMUM WORI | KING PRESSU | IRES | | | | |
|-----------------------|---------|--|-------|-------|------------|-------------------------------|-------|-------|-------|-------|-------|
| a 1 | | Type of Tubing and Wall Thickness (Inches) | | | | | | | | | |
| Service Conditions | Tube OD | Copper – Dead Soft (Seamless) | | | | Copper – Half Hard (Seamless) | | | | | |
| OUNDITIONS | | .030" | .032" | .035" | .049" | .065" | .032" | .035" | .042" | .049" | .065" |
| | 1/8 | 4300 | | 5000 | | | 5000 | | | | |
| | 3/16 | 2850 | | 3300 | | | 3400 | | | | |
| | 1/4 | 2100 | 2250 | 2500 | | | 2500 | | | | |
| Orfet | 5/16 | | 1800 | 2000 | | | 2000 | | | | |
| Safety Factor 4-1 | 3/8 | | 1500 | 1650 | | | 1700 | 1850 | | | |
| | 1/2 | | 1100 | 1250 | | 2000 | 1250 | 1400 | | | 2600 |
| | 5/8 | | | 1000 | 1400 | 1800 | 1000 | | | 1500 | 2000 |
| | 3/4 | | | 850 | 1150 | 1500 | | | 1100 | | 1700 |
| | 7/8 | | | | | | | | | 1100 | 1500 |
| | 1/8 | 2800 | | 3350 | | | 3400 | | | | |
| | 3/16 | 1900 | | 2200 | | | 2250 | | | | |
| | 1/4 | 1430 | 1500 | 1650 | | | 1700 | | | | |
| | 5/16 | | 1200 | 1300 | | | 1350 | | | | |
| Safety Factor 6-1 | 3/8 | | 100 | 1100 | | | 1100 | 1200 | | | |
| | 1/2 | | 750 | 825 | | 1550 | 850 | 925 | | | 1750 |
| | 5/8 | | | 650 | 930 | 1200 | 675 | | | 1000 | 1350 |
| | 3/4 | | | 550 | 775 | 1000 | | | 725 | | 1100 |
| | 7/8 | | | | | | | | | 750 | 1000 |



Brass Hose Fittings

Use: For use with residential and commercial grade garden hose, all female hose thread connections require a rubber washer inserted prior to installation.

Design Features

- · Compatible with ANSF B1.20.1
- \cdot Low lead compliant

Operating Specifications

| Temperature: | -35° – 100°F at maximum operating pressures |
|-------------------|---|
| Working Pressure: | 75 PSI maximum, intermittent to 150 PSI |

| Fitting Material Specifications | | | |
|---------------------------------|--------|--|--|
| Body Low Lead Compliant Brass | | | |
| Hose Washer | Rubber | | |

| Sku | Description |
|-------------|---|
| PFXFFHDFN | Female Hose Adaptor 1/2" FIP x 3/4" FHT |
| PFXFMHDFN | Male Hose Adaptor 3/4" MHT x 1/2" FFIP |
| PFXMFHDFN | Female Hose Adaptor 3/4" FHT x 1/2" MIP |
| PFXMMHDFN | Male Hose Adaptor 3/4" MHT x 1/2" MIP |
| PFXMFMHFDFN | Male Hose Adaptor 3/4" MHT x 1/2" FIP (3/4" MIP) |
| PFXFFHFFN | Male Hose Adaptor 3/4" MHT x 3/4" FIP |
| PFXMFHFFN | Female Hose Adaptor 3/4" FHT x 3/4" MIP |
| PFXMMHFFN | Male Hose Adaptor 3/4" MHT x 3/4" MIP |
| PFXMHFFN | Male Hose Union 3/4" MHT x 3/4" MHT |
| PFXBFHDFN | Female Hose Swivel Barb Adaptor 3/4" FHT x 1/2" ID Hose Barb |
| PFXBFHEFN | Female Hose Swivel Barb Adaptor 3/4" FHT x 5/8" ID Hose Barb |





| Sku | Description |
|-------------|---|
| PFXBFHFFN | Female Hose Swivel Barb Adaptor 3/4" FHT x 3/4" ID Hose Barb |
| PFXFFHSDFN | Female Swivel Hose Adaptor 3/4" FHT x 1/2" FIP |
| PFXFHFHSFFN | Female Swivel Hose Union 3/4" FHT x 3/4" FHT |
| PFXFFHSFFN | Female Swivel Hose Adaptor 3/4" FHT x 3/4" FIP |
| PFXMHAAN | Male Hose Barb Adaptor 1/8" ID Hose Barb x 1/8" MIP |
| PFXBMHFFN | Male Hose Barb Adaptor 3/4" MHT x 3/4" 5/8 ID Hose Barb |
| PFXHWFFN | Y Hose Fitting 3/4" FHT x 3/4" MHT x 3/4" MHT |
| PFXDEDN | Garden Hose Dishwasher Elbow 3/4" FHT x 1/2" OD Tube |
| PFXDEN | Garden Hose Dishwasher Elbow 3/4" FHT x 3/8" OD Tube |
| PFXGHCFN | Garden Hose Cap 3/4" FHT |
| PFRGHWN | Rubber Garden Hose Washer For 3/4" FHT |

Listings & Certifications

Low Lead Compliant ad product CSA certified to NSF/ANSI 372 – Drinking water system components – Lead Content, and conforms to the requirements for "lead free" plumbing products as defined by California, Vermont, Maryland, and Louisiana state law and by Section 1417 of the US Safe Drinking Water Act.

