GENERAL INFORMATION

ZAMAC HAMMER-SCREW®

Nail Anchor

PRODUCT DESCRIPTION

The Zamac Hammer-Screw is a unique, one-step nail drive anchor featuring a Phillips type head and a screw thread for use in concrete, block, brick or stone. It is available in 1/4" diameter and lengths ranging from 3/4" to 3". With a body formed from corrosion resistant Zamac alloy and a zinc plated carbon steel drive screw, this anchor has been developed as an improvement over standard nailin anchors.

The Zamac Hammer-Screw has been designed to provide a removable anchor with higher tension load capacities compared with traditional nailin when installed in concrete. The anchor is not recommended for overhead, life-safety or sustained tensile loading applications (see performance data section).

Drywall track

Maintenance

Surveillance equipment

Light gage attachments

GENERAL APPLICATIONS AND USES

- Brick ties and masonry anchorage
- Electrical fixtures
- Signage
- Flashing

FEATURES AND BENEFITS

- + General purpose anchoring
- + Installs in a variety of base materials
- + Removable anchor screw can be backed out with a Phillips head driver

APPROVALS AND LISTINGS

• Federal GSA Specification - Meets the proof load requirements of FF-S-325C, Group V, Type 2, Class 3, (superseded) and CID A-A 1925A, Type 1

GUIDE SPECIFICATIONS

CSI Divisions: 03 16 00 - Concrete Anchors, 04 05 19.16 - Masonry Anchors and 05 05 19 - Post-Installed Concrete Anchors. Anchors shall be Zamac Hammer-Screw anchors as supplied by DEWALT, Towson, MD. Anchors shall be installed in accordance with published instructions and the Authority Having Jurisdiction.


INSTALLATION AND MATERIAL SPECIFICATIONS

Installation Specifications

Dimension	Anchor Diameter, d
Dimension	1/4
ANSI Drill Bit Size (in.)	1/4
Fixture Clearance Hole (in.)	5/16
Head Height (in.)	9/64
Head Width (in.)	35/64


Installation Guidelines

1. Drill a hole into the base material to a depth of at least 1/4" deeper than the required embedment. The tolerances of the drill bit used should meet the requirements of ANSI Standard B212.15. Remove dust and debris from the hole during drilling (e.g. dust extractor) or following drilling (e.g. suction, forced air) to extract loose particles created by drilling.




1-800-4 DEWALT

2. Insert the anchor through the fixture. Drive the screw into the anchor body to expand it. Be sure the head is seated firmly against the fixture and that the anchor is at the proper embedment. Take care not to overdrive the screw. This anchor is not recommended for installations at an angle or for use overhead.



Optional: To remove – Press a Phillips screw driver firmly into the screw head and turn counterclockwise. Remove the screw from the anchor body, then pry out the fixture and anchor body simultaneously by working the claw of a hammer under the fixture



General Information	1
Installation and	
Material Specifications	1
Performance Data	2
Design Criteria	3
Ordering Information	3



ZAMAC HAMMER-SCREW

ANCHOR MATERIALS

• Zamac Alloy body with Carbon Steel Drive Screw

ANCHOR SIZE RANGE (TYP.)

• 1/4" x 3/4" to 1/4" x 3" diameter

SUITABLE BASE MATERIALS

- Normal-Weight Concrete
- Concrete Masonry (CMU)
- Brick Masonry
- Stone

Material Specifications

Anchor Component	Mushroom Head Carbon Steel Screw
Anchor Body	Zamac Alloy
Drive Screw	AISI 1018
Screw Plating/ Coating	ASTM B 633, SC1, Type III (Fe/Zn5)

PERFORMANCE DATA

Ultimate and Allowable Load Capacities for Zamac Hammer-Screw in Normal-Weight Concrete^{1,2,3,4,5}

D. H		Minimum Concrete Compressive Strength, f 'c											
Rod/ Anchor	Min. Embed.			4,000 psi			6,000 psi						
Diameter	Diameter Depth d h√ in. in. (mm) (mm)	Ten	sion	Sh	ear	Ten	sion	Sh	ear	Ten	sion	Sh	ear
in.		Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)
	5/8	675	170	650	165	850	215	880	220	890	225	880	220
	(16)	(3.0)	(0.8)	(2.9)	(0.7)	(3.8)	(1.0)	(3.9)	(1.0)	(4.0)	(1.0)	(3.9)	(1.0)
	3/4	790	200	805	200	1,135	285	1,115	280	1,190	300	1,115	280
	(19)	(3.5)	(0.9)	(3.6)	(0.9)	(5.0)	(1.3)	(5.0)	(1.2)	(5.3)	(1.3)	(5.0)	(1.2)
	7/8	930	235	990	250	1,205	300	1,230	310	1,250	315	1,230	310
	(22)	(4.1)	(1.0)	(4.4)	(1.1)	(5.4)	(1.3)	(5.5)	(1.4)	(5.6)	(1.4)	(5.5)	(1.4)
1/4	1-1/8	1,220	305	1,365	340	1,350	340	1,470	370	1,450	365	1,470	370
(6.4)	(29)	(5.4)	(1.4)	(6.1)	(1.5)	(6.0)	(1.5)	(6.5)	(1.6)	(6.4)	(1.6)	(6.5)	(1.6)
	1-3/8	1,325	330	1,555	390	1,450	365	1,645	410	1,530	385	1,645	410
	(35)	(5.9)	(1.5)	(6.9)	(1.7)	(6.4)	(1.6)	(7.3)	(1.8)	(6.8)	(1.7)	(7.3)	(1.8)
	1-3/4	1,480	370	1,840	460	1,600	400	1,910	480	1,660	415	1,910	480
	(44)	(6.6)	(1.6)	(8.2)	(2.0)	(7.1)	(1.8)	(8.5)	(2.1)	(7.4)	(1.8)	(8.5)	(2.1)
	1-7/8	1,480	370	1,840	460	1,600	400	1,910	480	1,660	415	1,910	480
	(48)	(6.6)	(1.6)	(8.2)	(2.0)	(7.1)	(1.8)	(8.5)	(2.1)	(7.4)	(1.8)	(8.5)	(2.1)

1. Tabulated load values are for anchors installed in concrete. Concrete compressive strength must be at the specified minimum at the time of installation.

2. Allowable load capacities listed are calculated using an applied safety factor of 4.0. Anchors are not recommended for use overhead or for life safety. Consideration of safety factors of 20 or higher may be necessary depending on the application, such as in sustained tensile loading applications.

3. Linear interpolation may be used to determine allowable loads for anchors at intermediate embedment depths and compressive strengths.

4. The tabulated load values are applicable to single anchors installed at critical edge and spacing distances. Allowable load capacities are multiplied by reduction factors when anchor spacing or edge distances are less than critical distances.

5. Anchors installed flush with face or end of concrete surface.

Ultimate and Allowable Load Capacities for Zamac Hammer-Screw in Hollow Concrete Masonry^{1,2,3,4}

Nominal	Minimum	f´m ≥ 1,500 psi (10.4 MPa)					
Anchor Diameter	Embedment Depth	Ultimat	e Load	Allowable Load			
d in. (mm)	h√ in. (mm)	Tension Ibs. (kN)	Shear Ibs. (kN)	Tension Ibs. (kN)	Shear Ibs. (kN)		
	5/8 (15.9)	420 (1.9)	1,160 (5.2)	85 (0.4)	230 (1.0)		
	3/4 (19.1)	825 (3.7)	1,215 (5.5)	165 (0.7)	245 (1.1)		
1/4	1 (25.4)	1,000 (4.5)	1,265 (5.7)	200 (0.9)	255 (1.1)		
(6.4)	1-1/8 (28.6)	1,090 (4.9)	1,290 (5.8)	220 (1.0)	260 (1.2)		
	1-3/8 (34.9)	1,145 (5.2)	1,345 (6.1)	230 (1.0)	270 (1.2)		
	1-1/2 (38.1)	1,145 (5.2)	1,345 (6.1)	230 (1.0)	270 (1.2)		

1. Tabulated load values are for anchors installed in minimum 6-inch wide, Grade N, Type II, medium and normal-weight and lightweight concrete masonry units. Mortar must be Type N, S or M. Masonry compressive strength must be 1,500 psi minimum at the time of installation. Hollow masonry cells may also be grouted or solid.

2. The tabulated values are for anchors installed at a minimum of 16 anchor diameters on center for 100 percent capacity. Spacing distances may be reduced to 8 anchor diameters on center provided the capacities are reduced by 50 percent. Linear interpolation may be used for intermediate spacing.

 Allowable load capacities listed are calculated using and applied safety factor of 5.0. Anchors are not recommended for use overhead or for life safety. Consideration of safety factors of 20 or higher may be necessary depending upon the application such as in sustained tensile loading applications.

4. Anchors installed flush with face or end of masonry surface.

NICA

Vail Anchor

ZAMAC HAMMER-SCREW®

Ultimate and Allowable Load Capacities for Zamac-Hammer Screw in Solid Clay Brick Masonry^{1,2,3,4}

Nominal	Minimum	f'm ≥ 1,500 psi (10.4 MPa)					
Anchor Diameter	Embedment Depth	Ultima	te Load	Allowable Load			
d in. (mm)	h√ in. (mm)	Tension Ibs. (kN)	Shear Ibs. (kN)	Tension Ibs. (kN)	Shear Ibs. (kN)		
	5/8 (15.9)	680 (3.1)	1,025 (4.6)	135 (0.6)	205 (0.9)		
1/4 (6.4)	3/4 (19.1)	930 (4.2)	1,200 (5.3)	185 (0.8)	240 (1.1)		
	1 (25.4)	990 (4.5)	1,350 (6.0)	200 (0.9)	270 (1.2)		
	1-1/8 (28.6)	1,040 (4.7)	1,350 (6.0)	210 (0.9)	270 (1.2)		
	1-3/8 (34.9)	1,150 (5.2)	1,350 (6.0)	230 (1.0)	270 (1.2)		
	1-1/2 (38.1)	1,260 (5.7)	1,350 (6.0)	250 (1.1)	270 (1.2)		

1. Tabulated load values are for anchors installed in multiple wythe, minimum Grade SW, solid clay brick masonry walls conforming to ASTM C 62. Mortar must be minimum Type N. Masonry compressive strength must be at the specified minimum at the time of installation (f'm \geq 1,500 psi).

2. The tabulated values are for anchors installed at a minimum of 16 anchor diameters on center for 100 percent capacity. Spacing distances may be reduced to 8 anchor diameters on center provided the capacities are reduced by 50 percent. Linear interpolation may be used for intermediate spacing.

3. Allowable load capacities listed are calculated using and applied safety factor of 5.0. Anchors are not recommended for use overhead or for life safety. Consideration of safety factors of 20 or higher may be necessary depending upon the application such as in sustained tensile loading applications.

4. Anchors installed flush with face or end of masonry surface.

DESIGN CRITERIA

ANCHORS & FASTENERS

Combined Loading

For anchors loaded in both shear and tension, the combination of loads should be proportioned as follows:

 $\left(\frac{Nu}{Nn}\right) + \left(\frac{Vu}{Vn}\right) \le 1$

Where:

Nn = Allowable Tension Load

 N_{μ} = Applied Service Tension Load V_{μ} = Applied Service Shear Load Vn = Allowable Shear Load

Load Adjustment Factors for Spacing and Edge Distances in Normal-Weight Concrete¹

Anchor Dimension	Load Type	Critical Distance (Full Anchor Capacity)	Critical Load Factor	Minimum Distance (Reduced Capacity)	Minimum Load Factor
Spacing (s)	Tension and Shear	s _{cr} = 10d	$F_{NS} = F_{VS} = 1.0$	$S_{min} = 5d$	F _{NS} = F _{VS} = 0.50
Edga Distance (a)	Tension	$c_{cr} = 12d$	$F_{NC} = 1.0$	$c_{min} = 6d$	$F_{\text{NC}} = 0.80$
Edge Distance (c)	Shear	$c_{cr} = 12d$	$F_{VC} = 1.0$	$c_{min} = 6d$	$F_{vc} = 0.50$

1. Allowable load values found in the performance data tables are multiplied by reduction factors when anchor spacing or edge distances are less than critical distances. Linear interpolation is allowed for intermediate anchor spacing and edge distances between critical and minimum distances. When an anchor is affected by both reduced spacing and edge distance, the spacing and edge reduction factors must be combined (multiplied). Multiple reduction factors for anchor spacing and edge distance may be required depending on the anchor group configuration.

ORDERING INFORMATION

Mushroom Head with No. 2 Phillips Head Screw

Cat No.	Anchor Size	Drill Diameter	Std. Box	Std. Carton	Wt./100			
2839	1/4" x 3/4"	1/4"	100	500	1-1/2			
2840	1/4" x 1"	1/4"	100	500	1-3/4			
2842	1/4" x 1-1/4"	1/4"	100	500	2-1/4			
2844	1/4" x 1-1/2"	1/4"	100	500	2-1/2			
2846	1/4" x 2"	1/4"	100	500	3			
2848	1/4" x 2-1/4"	1/4"	100	500	3-1/2			
2850	1/4" x 3"	1/4"	100	500	4-1/4			
The published size incl	The published size includes the diameter and length of the anchor measured from under the shoulder of the anchor body.							



maotor r aon				
Cat No.	Anchor Size	Drill Diameter	Std. Carton	Wt./100
2939	1/4" x 3/4"	1/4"	1,000	1-1/2
2940	1/4" x 1"	1/4"	1,000	1-3/4
2942	1/4" x 1-1/4"	1/4"	1,000	2-1/4
2944	1/4" x 1-1/2"	1/4"	1,000	2-1/2
2946	1/4" x 2"	1/4"	1,000	3
2948	1/4" x 2-1/4"	1/4"	1,000	3-1/2
2949	1/4" x 3"	1/4"	1,000	4-1/4
The second state of the second			and a state of the state of the state	

The published size includes the diameter and length of the anchor measured from under the shoulder of the anchor body.

