# **KOHLER**<sub>®</sub>

## Corbelle® Comfort Height®

#### Elongated chair height toilet bowl K-4144

#### Features

- Elongated bowl offers added room and comfort.
- Skirted trapway simplifies cleaning.
- Revolution 360<sup>®</sup> swirl flushing technology generates a forceful swirling motion to keep the bowl cleaner, longer.
- Comfort Height<sup>®</sup> feature offers chair-height seating that makes sitting down and standing up easier for most adults.
- 2-1/8" (54 mm) fully-glazed trapway.
- Combines with the K-4143/4143-RA tank to create a complete K-3814/3814-RA Corbelle toilet.

#### Technology

 CleanCoat<sup>™</sup> technology inhibits the growth of water scale and mineral stains for improved ease of cleaning.

#### Installation

- Patented ReadyLock<sup>™</sup> installation system is a simple solution for skirted toilets that saves time, hassle and eliminates the need to drill into the floor for a standard 12" (305 mm) rough-in.
- Standard 12" (305 mm) rough-in.
- 10" and 14" (254 mm and 356 mm) rough-in kits available.
- Seat not included.
- ReadyLock<sup>™</sup> installation system offers easy, intuitive installation with no need to drill holes in floor for standard 12" rough-ins.

#### **Recommended Products/Accessories**

K-4143 Toilet tank, 1.28 gpf K-23726 Drain treatment

#### **Included Components**

Additional Components: ReadyLock™ installation system



#### Codes/Standards

ASME A112.19.2/CSA B45.1

## KOHLER<sup>®</sup> Toilets and Seats Limited Warranty

See website for detailed warranty information.

#### **Available Colors/Finishes**

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	95	lce™ Grey
	G9	Sandbar
	7	Black Black™





## Corbelle® Comfort Height®

Elongated chair height toilet bowl K-4144

No image available. This product is a component and not intended to be a standalone installation.

#### **Technical Information**

All product dimensions are nominal.Trap passageway:2-1/8" (54 mm)Rough-in:12" (305 mm)

#### Notes

Install this product according to the installation instructions.

