


Specialty Products™



SPECIFICATION

Furnish and install high-impact plastic Washing Machine Outlet Box with brass valves as manufactured by LSP Products Group/Specialty Products.

DESIGN FEATURES

- Patented box design provides left, center and right waste options.
- Box knockouts accept either waste or water lines.
- Built-in test cap in box.
- Adjustable faceplate accommodates up to 5/8" wall thickness.
- EZ-Turn Quarter-Turn Ball Valves made of durable brass resists cracking and corrosion and allows fingertip control of water flow.
- Simplex Valve consolidates hot and cold water connections into one lever-controlled unit.
- EZ-Turn valves have long-lasting o-rings and tough Teflon seats.
- Slim-line box profile allows for 1" backing.



3689 Arrowhead Drive, Carson City, NV 89706
 Phone (800) 854-3215 Fax (800) 243-1777
 E-mail sales@lspproducts.com Website www.lspproducts.com

Content matter is subject to change at any time. It is the user's responsibility to ensure the most updated revisions are obtained.
 SP/S-2037 (08-02) Rev 3

PLASTIC UNIVERSAL WASHING MACHINE OUTLET BOX


Specification Sheet

COMPLIANCES/LISTINGS


- IAPMO File #0901
- Valve also meets or exceeds:
 - ASME A112.18.1 Standard
 - NSF Standard 61

OPTIONAL


- Deep faceplates available, accommodates up to 1" wall thickness
- Replacement faceplates available:
 - White - Part No. OB-901
 - Beige - Part No. OB-900



Front View



Bottom View



Face Plate

Product Submittal	
Job Name	
Date	
Part Number	Quantity
Architect	
Contractor	

Specialty Products™


PLASTIC UNIVERSAL WASHING MACHINE OUTLET BOX Specification Sheet

Part No	Color	Description
WITHOUT VALVES		
OB-100	Beige	Without Valves
OB-101	White	Without Valves
WITH PEX VALVES		
<i>UNASSEMBLED</i>		
OB-321	White	Unassembled
<i>ASSEMBLED</i>		
OB-323	White	Center Outlet
OB-325	White	Left Outlet
OB-327	White	Right Outlet
WITH CPVC VALVES		
<i>UNASSEMBLED</i>		
OB-350	Beige	Unassembled
OB-351	White	Unassembled
<i>ASSEMBLED</i>		
OB-354	Beige	Left Outlet
OB-356	Beige	Right Outlet
OB-353	White	Center Outlet
OB-355	White	Left Outlet
OB-357	White	Right Outlet
WITH M.I.P. VALVES		
<i>UNASSEMBLED</i>		
OB-102	Beige	Unassembled
OB-103	White	Unassembled
<i>ASSEMBLED</i>		
OB-200	Beige	Center Outlet
OB-202	Beige	Left Outlet
OB-204	Beige	Right Outlet
OB-201	White	Center Outlet
OB-203	White	Left Outlet
OB-205	White	Right Outlet
WITH REHAU VALVES		
<i>UNASSEMBLED</i>		
OB-371	White	Unassembled
<i>ASSEMBLED</i>		
OB-373	White	Center Outlet
OB-375	White	Left Outlet
OB-377	White	Right Outlet
WITH WIRSBO VALVES		
<i>UNASSEMBLED</i>		
OB-331	White	Unassembled
<i>ASSEMBLED</i>		
OB-337	White	Right Outlet
OB-338	White	Center Outlet
WITH VIEGA PEX VALVES		
<i>UNASSEMBLED</i>		
OB-341	White	Unassembled
<i>ASSEMBLED</i>		
OB-343	White	Center Outlet

*Add "-T" to the end of the part number for Tract Pack (faceplates packaged separately)
*Add "-TOP" to the end of the part number for Top Mounted Valves

NEW: Thinner Design Allows

The Use Of Backing



Side View Installation INSTALLATION INSTRUCTIONS

1. Position box between studs to desired height.
2. Secure box to a backing board with screws or nail bracket(s) on box to front of stud(s). In both cases the front edge of the box should be flush with wall material.
3. Cut or punch opening in bottom box if necessary for 2" plastic drain pipe Solvent cement pipe to bottom of box.
4. When installing valves follow your local codes.
5. Install face plate by pushing plate into box until plate is flush against the wall material.

LSP
PRODUCTSGROUP

3689 Arrowhead Drive, Carson City, NV 89706
Phone (800) 854-3215 Fax (800) 243-1777
E-mail sales@lspproducts.com Website www.lspproducts.com

Content matter is subject to change at any time. It is the user's responsibility to ensure the most updated revisions are obtained.

SP/S-2037 (08-02) Rev 3