

INSTALLATION INSTRUCTIONS

Scensibles[®] LBM500 Liner Bags

ITEM# LBM500

Flexible open-end bag designed for nearly all types of receptacles, including recessed, wall mount, and dual-access.

Size: 10" x 4" x 12"

Case Pack: 500/case



■ STEP 1

Open the receptacle.



■ STEP 2

Open bag and place inside the receptacle. Fold top of the bag over the top of the receptacle.



■ STEP 3

Tuck the bag under the lid to hold the back in place.



■ STEP 4

To remove a filled liner bag, pull up on the bag to discard contents.

