

INSTALLATION INSTRUCTIONS

Scensibles® LBS500 Liner Bags

ITEM# LBS500

Tight-fitting open-end bag designed for Scensibles® CDW and HOSPECO HS-6140WP receptacles.

Size: 9.5" x 12"

Case Pack: 500/case



■ STEP 1

Open the receptacle and remove rigid liner from inside of receptacle.



■ STEP 2

Open bag and stretch to fit snugly on all four sides of the rigid liner.



■ STEP 3

Place rigid liner back into receptacle.



■ STEP 4

To remove a filled liner bag, pull up on the bag to discard contents.

